

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

10-01-1084

Status:

Active

Overview:

KK® Interconnect System

Description:

5.08mm Pitch KK® Crimp Terminal Housing, 8 Circuits



Series

image - Reference only

Documents:

- 3D Model

Product Specification PS-99020-0087 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

3001

Application

Power, Wire-to-Board

Overview

KK® Interconnect System

Product Name

KK®

UPC

800753612723

Physical

Circuits (maximum)

8

Color - Resin

Natural

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

No

Material - Resin

Nylon

Net Weight

2.228/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

5.08mm

Temperature Range - Operating

See Product Specification

Solder Process Data

Lead-free Process Capability

Wave Capable (TH only)

Material Info

Old Part Number

3001-08

Reference - Drawing Numbers

Product Specification

PS-99020-0087

Sales Drawing

SDE-3001-N*

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

3001Series

Mates With

3061 , 3003 , 3008

Use With

2478 Crimp Terminals for 18-24 AWG, 2578
Crimp Terminals for 22-26 AWG, 2878

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION