

Produkt Informationen



WDD 161V

Bestellnummer : **T0053280699**



Desoldering Station Set

Desoldering Station Digital 165 W, 230 V, Compressed Air or Inert Gas Operated

Technical Data

166 x 115 x 101 mm

Dimensions (L x W x H)

inch (L x W x H) 6.54 x 4.53 x 3.98

Mains Voltage: 230 V / 50 / 60 Hz
100 V / 50/60 Hz

Power Consumption: 165 W

Protection Class: 1 (Control) and 3 (Soldering Tool)

Fuse: T800 mA (230 V)
T1,6 A (100 V)
(5 x 20 in the power unit)

Temperature Regulation:

50°C - 450°C (122°F - 842°F)
(WSP 150: 50°C - 550°C)
(122°F - 1022°F)

Precision: ± 9°C (± 17°F)

Equipotential Bonding:

via 3,5 mm jack bushing in the button of the unit. (State upon delivery: hard grounded , plug is not inserted)