



Ty-Rap®

TY523MR

Premium cable tie with stainless steel locking barb to cover the most demanding applications.

T&B Catalog Number: TY523MR
EAN Number: 05414363065371
UPC Number: 78621056475
Description: Premium, standard cable tie, 92 x 2.4 mm, natural Polyamide 6.6



Technical Information

Type	standard
Material	Polyamide 6.6
Material Locking Barb	316 grade stainless steel
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	natural
Halogen free	yes
Silicone free	yes

Approvals

UL listed	E49405
Germanischer Lloyd approval	yes
Lloyds Register approval	yes
MIL Spec.	MS-3367-4
Other approval	BVQ

Ordering Information

Length (mm)	92
Width (mm)	2.4
Thickness (mm)	1
Max. Bundle Diameter (mm)	16
Min. Bundle Diameter (mm)	2
Min. Tensile Strength (N)	80
Quantity (pieces)	100
Packaging Type	Euroslot bag

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, WT193A
