





## 1.5W LED G5.3 Lamp

KLED1.5HIO/G5.3-White  
 KLED1.5HIO/G5.3-Blue  
 KLED1.5HIO/G5.3-Green  
 KLED1.5HIO/G5.3-Red  
 KLED1.5HIO/G5.3-Yellow  
 KLED1.5HIO/G5.3-Orange

### Product Code Format:

KLED□□HIO/□□□-□□□  
 |                      |                      |  
 Rated Lamp      Lamp Cap      Color  
 Wattage

### Features:

- Save energy up to 90% comparing with halogen lamps.
- Long Life of 30000h, 20 times longer than halogen lamp
- Popular G5.3 base and standard shape for direct replacement of halogen G5.3 lamp
- Instant start
- Not dimmable
- Lamp life may reduce when used in a enclosed fitting

### Specifications:

Rated Lamp Wattage	1.5W	Ambient Temperature	-20°C to 40°C
Equ. Watt	10W	LED Chip	Epistar
Number of LEDs	12pcs	Length	50mm
Voltage	12V	Diameter	50mm
Dimmable	No	Packaging type	Colour Box
Base	G5.3	Qty per Box	1
Life to 50% failure	30000hr	Qty per mid-Carton	10
Color	White/Blue/Green/Red/	Qty per Carton	50
	Yellow/Orange	Net weight Per piece	39g
CRI	76Ra(white)	Gross Weight per Carton	2.8kg
Lamp Luminous Flux	60lm(White)		
Lumen maintenance 8000h	95%		
Lumen maintenance 30000h	80%		