


EVEREADY BATTERY CO. Internet: www.energizer.com 1-800-383-7323 / USA 1-800-383-7323 / CANADA

+ 44 (0) 208 920 2306 / EUROPE

ENERGIZER NO. 362



Industry Standard Dimensions in mm (inches)



Silver Oxide (Zn/Ag₂0) **Chemical System:**

Designation: ANSY/ NEDA/1158SO, JEC-SR58

Battery Voltage: 1.55 Volts

Average Weight: 0.42 grams (0.015 oz.)


0.10 cubic centimeters (0.006 cubic inch) Volume:

Average Capacity: 27 mAh to 1.3 voits

(Rated at 68k ohms continuous at 21°C)

TYPICAL DISCHARGE CURVE

Simulated Test @ 21°C (70°F)



DESIGNED FOR USE ON CONTINUOUS LOW DRAIN

Simulated Application Test Estimated Average Service at 21°C (70°F)

Typical Drains			Cutoff Voltage
Schedule:	at 1.55V (milliamperes)	Load (ohms)	1.3V
24 hours/day	0.023	68,000	1,174 Hours

INTERNAL RESISTANCE: Closed circuit voltage no less than 0.90 volts on a load of 100 ohms at 21°C (70°F) for 0.1 to 2.0 seconds.

> Typical closed circuit voltage during discharge on a load of 2,000 ohms for 0.0078 seconds.

Depth of Discharge as Percent of Rated Capacity

Temperature	0%	40%	80%
21°C (70°F)	1.58V	1.56V	1.56V
-10°C (14°F)	1.53V	1.43V	1.44V

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved

Form No. EBC - 4321E Page 1 of 1