

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [09-50-8051](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 5 Circuits](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)
[Packaging Specification PK-41695-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [41695](#)
Application Power, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK® 396
UPC 800754227711

Physical

Breakaway No
Circuits (maximum) 5
Color - Resin Natural
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 1.746/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm
Temperature Range - Operating See Product Specification

Material Info

Old Part Number 41695-N-B05

Reference - Drawing Numbers

[Packaging Specification](#) PK-41695-001
[Product Specification](#) PS-08-50
[Sales Drawing](#) SD-41695



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[41695Series](#)

Mates With
KK® 396 Header [41791](#) , [41792](#) , [41671](#) ,
[41672](#) , [41661](#) , [41662](#)

Use With
KK® 396 Crimp Terminals, [2478](#) , [2578](#) ,
[6838](#) , [7258](#) , [45570](#)