

1195350006

6 Pole polyamide tab to tab terminal block 5 tabs per Pole 6.3x0.8 mm tab size 17.5a 450v


PRODUCT SPECIFICATIONS

Tracking resistance CTI (v)	250
Terminal screw material	M 4 zinc-plated steel
Comments	Photo is just a representative of terminal block, see line drawing for pole size and pitch
Number of poles	6
Tabs per pole	5
Tab size (mm)	6.3x0.8
Body material	Natural polyamide
Colour	Natural
Min conductor size (Sq mm)	0.75
Max conductor size (Sq mm)	1.5
Max current (A)	17.5
Max voltage (V)	450
Working temperature	T110
Pitch (mm)	11
Length (mm)	85