

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-58-0122

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 396 Crimp Terminal 2478, 18-24 AWG, Bag, Phosphor Bronze, 0.51µm Selective Gold (Au)



Series

image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-08-50 \(PDF\)](#)

General

Product Family

Crimp Terminals

Series

2478

Application

Power

Crimp Quality Equipment

Yes

Overview

KK® Interconnect System - Molex

Packaging Alternative

08-58-0121 (Reel)

Product Name

KK® 396

UPC

800754226998

Physical

Gender

Female

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Net Weight

0.150/g

Packaging Type

Bag

Plating min - Mating

0.381µm

Plating min - Termination

0.051µm

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

2.79mm max.

Wire Size AWG

18, 20, 22, 24

Wire Size mm²

N/A

Material Info

Old Part Number

2478-3-(550)L

Reference - Drawing Numbers

Product Specification

PS-08-50

Sales Drawing

SD-2478

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2478Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool

0011030016

Hand Crimper

0638117500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION