Safety Data Sheet according to (EC) No 1907/2006

TEROSON MS 939 WH known as TEROSTAT MS 939 WHITE DK310M

sds no. : 268236
V003.1
Revision: 10.12.2012
printing date: 21.01.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier
TEROSON MS 939 WH known as TEROSTAT MS 939 WHITE DK310M

1.2. Relevant identified uses of the substance or mixture and uses advised against
Intended use:
1-Component sealant

1.3. Details of the supplier of the safety data sheet
Henkel Limited
Apollo Court, 2 Bishop Square Business Park
AL10 9EY Hatfield

Great Britain

Phone: +44 (1707) 635000
Fax-no.: +44 (1707) 635099

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number
24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):
No data available.

Classification (DPD):
No classification required.

2.2. Label elements

Label elements (CLP):
No data available.

Label elements (DPD):
The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

Additional labeling:
Safety data sheet available for professional user on request.

2.3. Other hazards
None if used properly.

SECTION 3: Composition/information on ingredients

General chemical description:
Sealant
Base substances of preparation:
Silane-modified polyether

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Trimethoxyvinylsilane 2768-02-7	220-449-8 01-2119513215-52	< 5 %	Flammable liquids 3 H226 Acute toxicity 4; Inhalation H332

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Trimethoxyvinylsilane 2768-02-7	220-449-8 01-2119513215-52	< 5 %	Xn - Harmful; R10, R20

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:
Move to fresh air, consult doctor if complaint persists.

Skin contact:
Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:
Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:
Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed
No data available.

4.3. Indication of any immediate medical attention and special treatment needed
See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media
Suitable extinguishing media:
All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:
High pressure waterjet

5.2. Special hazards arising from the substance or mixture
In case of fire toxic gases can be released.

5.3. Advice for firefighters
Wear protective equipment.
Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures
Wear protective equipment.

6.2. Environmental precautions
Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up
Remove mechanically.
Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections
See advice in chapter 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Hygiene measures:
Do not eat, drink or smoke while working.
Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities
Ensure good ventilation/extraction.
Temperatures between + 10 °C and + 25 °C

7.3. Specific end use(s)
1-Component sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Trimethoxyvinylsilane 2768-02-7	aqua (freshwater)					0,34 mg/L	
Trimethoxyvinylsilane 2768-02-7	aqua (marine water)					0,034 mg/L	
Trimethoxyvinylsilane 2768-02-7	aqua (intermittent releases)					3,4 mg/L	
Trimethoxyvinylsilane 2768-02-7	STP					110 mg/L	
Trimethoxyvinylsilane 2768-02-7	sediment (freshwater)				0,27 mg/kg		
Trimethoxyvinylsilane 2768-02-7	sediment (marine water)				0,12 mg/kg		
Trimethoxyvinylsilane 2768-02-7	soil				0,046 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Trimethoxyvinylsilane 2768-02-7	worker	dermal	Long term exposure - systemic effects		0,69 mg/kg bw/day	
Trimethoxyvinylsilane 2768-02-7	worker	inhalation	Long term exposure - systemic effects		4,9 mg/m3	
Trimethoxyvinylsilane 2768-02-7	general population	dermal	Acute/short term exposure - systemic effects		26,9 mg/kg bw/day	
Trimethoxyvinylsilane 2768-02-7	general population	inhalation	Acute/short term exposure - systemic effects		93,4 mg/m3	
Trimethoxyvinylsilane 2768-02-7	general population	dermal	Long term exposure - systemic effects		0,3 mg/kg bw/day	
Trimethoxyvinylsilane 2768-02-7	general population	inhalation	Long term exposure - systemic effects		1,04 mg/m3	
Trimethoxyvinylsilane 2768-02-7	general population	oral	Long term exposure - systemic effects		0,3 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR; >= 1 mm thickness) or natural rubber (NR; >=1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR; >= 1 mm thickness) or natural rubber (NR; >=1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Protective goggles

Skin protection:

Wear protective equipment.

Advices to personal protection equipment:

Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	solid material pasty white
Odor	characteristic
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No flash point up to 100 °C
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density (20 °C (68 °F))	1,50 g/cm3
Bulk density	No data available / Not applicable
Viscosity (; 20 °C (68 °F))	200 - 300 pa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Solid content (105 °C)	98 %
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability
Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions
See section reactivity

10.4. Conditions to avoid
None if used for intended purpose.

10.5. Incompatible materials
None if used properly.

10.6. Hazardous decomposition products
No decomposition if used according to specifications.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:
To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

SECTION 12: Ecological information

General ecological information:
The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.
Do not empty into drains, soil or bodies of water.

12.1. Toxicity

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Trimethoxyvinylsilane 2768-02-7	LC50	191 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 100 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 100 mg/l	Algae	72 h		OECD Guideline 201 (Alga, Growth Inhibition Test)

SECTION 13: Disposal considerations

13.1. Waste treatment methods
Product disposal:
The valid EEC waste code numbers are not product-related but are largely source-related. These can be requested from the manufacturer.

In consultation with the responsible local authority, must be subjected to special treatment.

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %
(VOCV 814.018 VOC regulation CH)

VOC Paints and Varnishes (EU):

Product (sub)category: This product is not a subject of the Directive 2004/42/EC

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text
of all abbreviations indicated by codes in this safety data sheet are as follows:

R10 Flammable.
R20 Harmful by inhalation.
H226 Flammable liquid and vapour.
H332 Harmful if inhaled.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.