

Models...

ATB 25, 50 & 100

1/4", 3/8", 1/2" interchangeable ratchet heads come as standard available in N.m, lbf.in or lbf.ft versions

Want to know how to use this tool?



Watch our video



For Wrench End Fittings & Sockets... see pages 68 - 69



**Tool
Selector**

Visit www.torqueleader.com/tool-selector to check this is the right tool for your application?

Order now... call our Sales Hotline +44 (0) 1483 894 476

Order Code	Model	Calibrated Range				Drive	mm	kg	Accuracy	ISO 6789 Class
		ISO	Imperial							
050636	ATB 25 D	5-25 N.m	0.1 N.m	-	-	1/4"	345	1.11	+/- 4%	2A
050641	ATB 25 D	-	-	50-250 lbf.in	1 lbf.in	1/4"	345	1.11	+/- 4%	2A
050646	ATB 25 D	-	-	4-20 lbf.ft	0.1 lbf.ft	1/4"	345	1.11	+/- 4%	2A
050638	ATB 25 A	5-25 N.m	0.1 N.m	-	-	3/8"	345	1.12	+/- 4%	2A
050643	ATB 25 A	-	-	50-250 lbf.in	1 lbf.in	3/8"	345	1.12	+/- 4%	2A
050648	ATB 25 A	-	-	4-20 lbf.ft	0.1 lbf.ft	3/8"	345	1.12	+/- 4%	2A
050685	ATB 50	10-50 N.m	0.25 N.m	-	-	3/8"	365	1.14	+/- 4%	2A
050690	ATB 50	-	-	120-440 lbf.in	2 lbf.in	3/8"	365	1.14	+/- 4%	2A
050695	ATB 50	-	-	7-37 lbf.ft	0.125 lbf.ft	3/8"	365	1.14	+/- 4%	2A
050735	ATB 100	20-100 N.m	0.5 N.m	-	-	1/2"	400	1.30	+/- 4%	2A
050740	ATB 100	-	-	240-880 lbf.in	4 lbf.in	1/2"	400	1.30	+/- 4%	2A
050745	ATB 100	-	-	14-74 lbf.ft	0.25 lbf.ft	1/2"	400	1.30	+/- 4%	2A