


	N. C. I		347 : 17	D: :	D: ·	D: :	۱ ،	D 10 4 D 1
	Manufacturer		Weight	Dimension	Dimension	Dimension	,	RoHS & Reach
Description	Part No	Material	(Kilograms)	Height (mm)	Width (mm)	Depth (mm)	of Origin	Compliant
ABS IP54 Enclosure Clear	479-0140-0	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Black	479-0140-1	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Blue	479-0140-2	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Brown	479-0140-3	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Green	479-0140-4	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Red	479-0140-5	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure White	479-0140-6	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Yellow	479-0140-7	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Purple	479-0140-8	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Grey	479-0140-9	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Orange	479-0140-10	ABS	0.30	76	51	28	GB	YES
ABS IP54 Enclosure Cream	479-0140-11	ABS	0.30	76	51	28	GB	YES




OPTIONAL EXTRAS


Stick on feet 12mm round x 4mm deep part no - FIX173 Also available in anti static







Α3



ABS Enclosure ±0.5mm ±0.1mm ±0.03mm 02 479-0140 Specification SCALE:1:1 SHEET 1 OF 1