

Ring Spanners



Nickel and chrome plated with highly polished finish. Dynamic-Drive-Profile up to 36 x 41mm and all imperial sizes. Deep offset. Conforms to DIN838/ ISO1085.

488342

| Number | Size (mm) | Order code | Price Each |
|----------|-----------|------------|------------|
| 2M-8-10 | 8 x 10 | 135-6183 | |
| 2M-10-11 | 10 x 11 | 135-6184 | |
| 2M-10-13 | 10 x 13 | 135-6186 | |
| 2M-12-13 | 12 x 13 | 135-6187 | |
| 2M-13-17 | 13 x 17 | 135-6188 | |
| 2M-17-19 | 17 x 19 | 135-6189 | |
| 2M-18-19 | 18 x 19 | 135-6190 | |
| 2M-19-22 | 19 x 22 | 135-6191 | |
| 2M-19-24 | 19 x 24 | 135-6192 | |
| 2M-24-26 | 24 x 26 | 135-6193 | |
| 2M-24-27 | 24 x 27 | 135-6194 | |
| 2M-24-30 | 24 x 30 | 135-6195 | |
| 2M-27-30 | 27 x 30 | 135-6196 | |
| 2M-30-32 | 30 x 32 | 135-6198 | |
| 2M-30-36 | 30 x 36 | 135-6199 | |
| 2M-32-36 | 32 x 36 | 135-6200 | |
| 2M-36-41 | 36 x 41 | 135-6202 | |
| 2M-41-46 | 41 x 46 | 135-6204 | |
| 2M-46-50 | 46 x 50 | 135-6205 | |