

Data Sheet WD1000M UK/EU Dual Cordset

Weller part no.	T0053408399
Description	Single channel solder station with micro soldering iron
Type	WD1000M
Comprises	WD1M power unit with high speed regulation WMRP miniature soldering iron with RT3 solder tip WDH 50 safety rest with stop / go function
Power rating	Soldering iron 40W / 24V 50Hz Power unit 160W
Supply required	230V 50Hz
Mains lead	fitted with UK plug
Temperature range	50C – 450C
Temperature tolerance	+/- 2% of max temperature
Temperature stability	+ /- 6C
Temperature pre- sets	3 (selectable)
Temperature display	LCD digital
Temperature setting	up / down push buttons
Features	temp lock / temp set back/ temp off set/temp window/auto off/ tool recognition
Can be used with	WMRT thermal tweezer and all silver line tools up to 150 W rating
ESD safe	
Safety Class	1 (power unit)

