

MAINNING CO., LTD.

Office: Room No.1105, Pingan Mansion, No.396 Kaiming Street, Ningbo, China
Tel:0086-574-87288314,87255118
E-mail: mainning@mail.nbptt.zj.cn

P. C. : 315000

Fax: 0086-574-87343958

MAINNING


Product Code: 9842 Belden Equivalent

Page:1/1

1.--/ CONSTRUCTION

Item	Description
1. Conductor	24AWG(7/0.20mm) stranded Tinned Copper
2. Insulation	Colour code PE, Nominal thickness: 0.60mm; Colour code: (White with Blue line, Blue with White line), (White with Orange line, Orange with White line)
Pair Number	2 Pairs, twisted pairs, White with Blue line and Blue with White line twisted pair, White with Orange line and Orange with White line twisted pair
3. Shield- foil	Overall Overlapped Aluminium-polyester Foil, 100% coverage
4. Drain Wire	24AWG(7/0.20mm) stranded Tinned Copper
5. Shield- Braid	Overall braid 16/7/0.12mm Tinned Copper, Coverage: 90%;
6. Jacket	Grey PVC, Nominal thickness: 0.89mm; Overall Diameter: 8.64+/-0.20mm

2.--/ DESIGN



3.--/ CHARACTERISTICS

Nominal Capacitance	12.800pF/Feet
Nominal Conductor DCR	24.000 Ohm/1000Feet
Nominal Velocity of Propagation	66.0%
Nominal Impedance	120.0 Ohms

4.--/ PACKING

Description	Size(Flange Dia. X Width)
500M Plywood Drum packing	mm X mm
1000M Plywood Drum packing	560mm X 420mm

Drawn by	Date	Checked	Approved
Xu Hualing	29th Jul.,2005	Wang Yangying	郑松林
MAINNING CO., LTD.			
Drawing Number : 98420			
Revision Level: Revised		Page 1 of 1	