

Item no. 216-204



Ferrule; sleeve for 1.5 mm² / awg 16; insulated; electro-tin plated

Name	Value	Unit
Color	black	
Stripped length from (1) [mm]	10	mm
Stripped length up to (1) [mm]	10	mm
Fire load [MJ]	0.002	MJ
Weight [g]	0.125	g
Diameter [mm]	4	mm
Diameter 1 [mm]	3.4	mm
Diameter 2 [mm]	1.8	mm
Length [mm]	14	mm
Length 1 [mm]	8	mm