



- Ideal for employees to check out tools from tool cribs
- Applications and industries: electricians, carpenters, contractors, maintenance, ironworkers, artisans, masonry, field service technicians
- Perfect for organizing and issuing tools to operators
- Constructed of durable, blue vinyl
- Made of high-performance, flexible, static dissipative fabric with buried conductive layer
- Rtt: 1×10^4 to $< 1 \times 10^{11}$ ohms per per ANSI/ESD S4.1
- Rolls up for easy storage; hook and loop secures closure
- Pockets designed to store up to 18 tools
- Unrolled Dimensions: 20" x 12.5"
- Made in the United States of America

Properties

Weight	12.5 - 14.5 oz/yd ² (FSTM191.5041)
Nominal Thickness	0.026 inch
Tensile	100 lbs (FSTM191.5100)
Tongue Tear	6 lbs (FSTM191.5134)

35981 Static Dissipative Tool Roll-Up Pouch

Dimension tolerance is $\pm 1/4$ "

Specifications and procedures subject to change without notice.



Made in the United States of America

Static Dissipative Tool Roll-Up Pouch

3651 WALNUT AVE., CHINO, CA 91710
PHONE: (909) 627-2453
WEBSITE: MendaTools.com

DRAWING NUMBER
35981

DATE:
February
2014

MENDA