

MINIATURE LAMP (335) Details



Part #	335				
Description	T1 3/4 MID SCREW 28V .04A .34CP				
Bulb Shape	T-1 3/4	Filament	C-2F	Base Style	Midget Screw (E5)
Glass Diameter (in)	0.22	MOL [†] (in)	0.72	LCL ^{††} (in)	0.52
Glass Diameter (mm)	5.5	MOL (mm)	18.30	LCL (mm)	13.21
Volts	28	MSCP [‡]	0.34	Avg Life Hrs	4000
Watts	1.12	Amps	0.04	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.