

## MINIATURE LAMP (51) Details



<b>Part #</b>	<b>51</b>				
<b>Description</b>	<b>G3 1/2 M BAY 7.5V .22A 1CP</b>				
<b>Bulb Shape</b>	G-3 1/2	<b>Filament</b>	C-2R	<b>Base Style</b>	Miniature Bayonet (BA9s)
<b>Glass Diameter (in)</b>	0.46	<b>MOL<sup>†</sup> (in)</b>	0.94	<b>LCL<sup>††</sup> (in)</b>	0.50
<b>Glass Diameter (mm)</b>	11.7	<b>MOL (mm)</b>	23.90	<b>LCL (mm)</b>	12.70
<b>Volts</b>	7.5	<b>MSCP<sup>‡</sup></b>	1	<b>Avg Life Hrs</b>	1000
<b>Watts</b>	1.65	<b>Amps</b>	0.22	<b>RoHS Compliant</b>	

**† MOL (Maximum Overall Length):**

The overall length of a lamp, from the top of the shell to the bottom of the base.

**‡ MSCP (Mean Spherical Candlepower):**

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

**†† LCL (Light Center Length):**

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.