

MINIATURE LAMP (756) Details



Part #	756				
Description	T3 1/4 M BAY 14V .08A .31CP				
Bulb Shape	T-3 1/4	Filament	C-2F	Base Style	Miniature Bayonet (BA9s)
Glass Diameter (in)	0.39	MOL[†] (in)	1.19	LCL^{††} (in)	0.63
Glass Diameter (mm)	10	MOL (mm)	30.20	LCL (mm)	16.00
Volts	14	MSCP[‡]	0.31	Avg Life Hrs	15000
Watts	1.12	Amps	0.08	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.