

MINIATURE LAMP (81) Details



Part #	81				
Description	G6 SC BAY 6.5V 1.02A 6CP				
Bulb Shape	G-6	Filament	C-2R	Base Style	S.C. Bayonet (BA15s)
Glass Diameter (in)	0.75	MOL[†] (in)	1.44	LCL^{††} (in)	0.75
Glass Diameter (mm)	19	MOL (mm)	36.56	LCL (mm)	19.10
Volts	6.5	MSCP[‡]	6	Avg Life Hrs	500
Watts	6.63	Amps	1.02	RoHS Compliant	Yes

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.