



5" Open Frame Midrange

MCM Part #: 54-310 | MCM Audio Select Part #: 54-310



5" Open Back Midrange

Poly treated paper cone midrange is perfect in a variety of home or pro sound three-way speaker applications, as well as use in a multi-driver automotive system. Open frame design allows extended low frequency response.

Features:

- Poly treated paper cone
- Foam surround
- Stamped steel basket
- 1" voice coil
- 13.3oz. magnet

Specifications:

- Frequency response: 100Hz ~ 10KHz
- Impedance: 8ohm
- Re: 7.0ohm
- Power handling: RMS/peak 50W/70W
- Sensitivity SPL 1W/1 meter: 93dB
- Fs: 104Hz
- Qts: 0.85
- Qes: 1.11
- Qms: 3.6
- Vas: 3.48(l)
- Sd: 0.0072m²
- Xmax: 1.0mm