



6" (152 mm) Slip-Joint Pliers

Cat. No. D511-6

Product Features

- Shear-type cutter for precision wire cutting.
- Two versatile jaw positions.
- Serrated jaws provide sure-gripping power.
- Nickel-chrome plated for long life.
- Knurled handles for greater leverage.



Jaw Length: 1-3/16" (30 mm)

Jaw Width: 1-3/16" (30 mm)

Jaw Thickness: 3/8" (10 mm)

Handle Finish: plastic-dipped

Overall Length: 6-9/16" (167 mm)

Handle Color: blue

Weight (lbs.): .39