



E25100

iQ Magnifier LED Lamp with its modern, sleek ergonomic design has a large 1.75x crystal clear lens and 60 ultra bright daylight LED's for accurate viewing of details.

Perfect for all industrial purposes, clinics, laboratories, beauty salons and for the visually impaired.

It has a flexible joint between the head and spring balanced arm, this gives effortless movement and long reach with accurate positioning and no drift.

iQ has 60 LED's which have a life expectancy of up to 20,000 hours or over 20 years use. No bulb or tube to replace.



60 LEDs



90% less energy



FreeMotion™
Head-joint



Metal table
clamp



Powerful 7"
magnifier



Overview

- 60 daylight premium LED's
- 4 stepped dimmer
- 17.5cm (7") lightweight lens with anti-scratch coating
- Quick swap lens system - 5D & 12D optional lenses available separately
- Effortless free-motion movement head and arm. Hold any position without drift
- Reinforced heavy duty arm with sealed joints, solid pivots and side covers
- Long reach 118cm (46.5") max
- LED's never need replacing
- Lux at 15cm 6,330 max



Technical information

Packaging information

Item code	E25100
Colour box width	605mm (23.82 in)
Colour box depth	100mm (3.94 in)
Colour box height	460mm (18.11 in)
Total packed weight	4.6kg (10 lbs)
Products per carton	2

Product information

Assembled Width	23.0cm (9 in)
Assembled Height	57.0cm (22½ in)
Assembled Depth	90.0cm (35½ in)
Assembled Weight	3.8kg (8½ lbs)
Length of cable	2.5m
Main colour	Grey/White

Light output information

Light source type	LED
Total wattage	12.0w
Colour temperature	6,000 - 6,500K

Magnifier info

Main lens size	17.5cm (7 in)
Main lens magnification	1.75x

Contact us

The Daylight Company Ltd
 Info.uk@daylightcompany.com
 UK + 44 (0)20 8964 1200
 FR 0825 00 49 46
 DE 0800 329 2667

