



Tenma 72-10415

### SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	220mV/2.2V/22V/220V/1000V	±(0.1%+2)
AC Voltage	220mV/2.2V/22V/220V/750V	±(0.8%+10)
DC Current	200μA/2200μA/22mA/220mA/2.2A/10A	±(0.5%+10)
AC Current	220μA/2200μA/22mA/220mA/2.2A/10A	±(0.8%+10)
Resistance	220 Ω /2.2k Ω /22k Ω /220k Ω /2.2M Ω /22M Ω /220M Ω	±(0.5%+10)
Capacitance	22nF/220nF/2.2μF/22μF/220μF/2.2mF/22mF/220mF	±(3.0%+5)
Frequency	10Hz-220MHz	±(0.01%+5)
<b>Special Functions</b>		
Display Count		22000
Auto Range		√
True RMS		√
Bandwidth (Hz)	45Hz-10KHz	√
Duty Cycle	0.1%~99.9%	√
Diode		√
Continuity Buzzer		√
Low Battery Indication	≅ 7.5V	√
Data Hold		√
Relative Mode		√
Peak Value		√
RS-232		√
LCD Backlight		√
Analogue Bar Graph	46	√
Input Protection		√
Input Impedance for DCV	Around :10MΩ	√
<b>GENERAL CHARACTERISTICS</b>		
Power	9V Battery (6F22)	
LCD Size	65 x 43mm	
Product Colour	Orange and Grey	
Product Net Weight	370g	
Product Size	180 x 87 x 47mm	
Standard Accessories	Battery, Test Lead, Multi-Purpose Socket, RS-232 Interface Cable, PC Software CD	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	20pcs	
Standard Carton Measurement	465 x 335 x 345mm	
Standard Carton Gross Weight	12kg	