KEMET Part Number: C052K103K1X5CA

(CK05BX103K)

Capacitor, ceramic, 0.01 uF, +/-10% Tol, 100V, BX, Lead Spacing=0.2"



General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.01 uF
Lead Spacing:	0.2"
Voltage:	100V
Temperature Coefficient:	BX
Tolerance:	+/-10%
Body Type:	Radial Molded
Lead Type:	Standard Leads
Lead Form:	Hockey Stick
Termination Type:	Tin-Lead (SnPb)

Dimensions (in)		
Symbol	**Dimension**	**Tolerance**
L	0.19	+/-0.01
H	0.235	+/-0.01
T	0.09	+/-0.01
S	0.2	+/-0.015
LL	1.25	MIN
F	0.025	+0.004/-0.002
K	0.19	+/-0.01
G	0.045	MAX

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

Notes:
-Note A: Center line of the leads will be within 0.03 in [0.76 mm] of the center line of the body.

-Lead length shown is for parts supplied in bulk. See packaging specifications for lead lengths when not provided in bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006-2014 IntelliData.net