# 9050JCK12V20 TIMER RELAY 240VAC 10AMP +OPTIONS

## **NATO** products



### Main

Commercial Status	Commercialised
Range of product	9050JCK
Product or component type	Timer
[In] rated current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Control circuit voltage	110 V DC 120 V AC
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	8
Shape of pin	Tubular
Product certifications	CE CSA UL listed
Time delay type	On-delay
Time delay range	0.330 s
-	

#### Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS	
Discount Schedule	CP2	
GTIN	00785901032557	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.24	
Product availability	Stock - Normally stocked in distribution facility	
Returnability	Υ	
Country of origin	US	

#### Offer Sustainability

<u> </u>	
Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0627 - Schneider Electric declaration of conformity

#### Contractual warranty

Ochtraotaar Warranty		
Period	18 months	