

Main

Commercial Status	Commercialised
Range of product	Harmony XAC
Product or component type	Head for pushbutton
Component name	XACA
Marking	Unmarked
Operator additional information	Booted
Cap/Operator or lens colour	Black
Product compatibility	XACA..
Sale per indivisible quantity	10

Complementary

Product mounting	Front mounting
Product weight	0.01 kg

Environment

Standards	CSA C22-2 No 14 EN/IEC 60204-32 EN/IEC 60947-5-1 UL 508
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

Contractual warranty

Period	18 months
--------	-----------