

MDR-V55

Take beats from your decks to the streets



Foldable headphones with 40mm driver unit, neodymium magnet and 1.2m cord

- Take them anywhere with a foldable design
- Crisp, dynamic sound thanks to a neodymium driver
- Minimum background noise with closed headphones

Product awards and reviews



Pocket-Lint, Hot Product, May 2012

"All in all, if you want some headphones, DJ or not, that sound great and pack up nicely, then the Sony MDR-V55 are definitely worth a look."

Features

Look good while you DJ

These sleek, curved headphones will add style to your DJ set and are available in four choices of colour

Easy to carry and store

A foldable design makes for easy storage, simply fold and store them in your bag when you're not listening to music

Don't miss a beat

The reversible earcup and the single-sided 1.2m cord make it easy for one-ear DJ listening

Give your beats full attention

Focus on fine-tuning and mixing thanks to noise isolating closed earphones

Turn up the bass, experience the treble

Experience rich bass thanks to a 40mm neodymium driver and a frequency range of up to 25,000Hz for powerful treble

Hear every detail

Listen to club tracks with high power input of up to 1,000mW and sensitive 105db/mW, for precise sound no matter what the volume

Comfortable listening

Whether you're at the decks or on the go, a wide moulded headband and cushioned earcups give the comfort you need

Specifications

General Data	
Open Air Type	NO
Dynamic Type	YES
Circum Aural Type	YES
Capacity (mW)	1000
Driver unit (mm)	40
Diaphragm	PET
Frequency (Hz)	5 - 25,000
Sensitivity (dB/mW)	105
Magnet	neodymium
Impedance (Ohm)	40
Volume control	NO
Cord type	Flat cord
Cord length (m)	1.2
Plug	Gold plated L shaped stereo mini
Weight (g)	220