

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [22-01-3097](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Housing, Friction Ramp, 9 Circuits](#)



Series

image - Reference only

Documents:

[3D Model](#) [Packaging Specification PK-2695-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [2695](#)
Application Signal, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK® 254
UPC 800753593893

Physical

Circuits (maximum) 9
Color - Resin Natural (White)
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 0.969/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating See Product Specification

Material Info

Old Part Number 2695-09RP

Reference - Drawing Numbers

Packaging Specification PK-2695-001
Product Specification PS-10-07
Sales Drawing SD-2695

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[2695Series](#)

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal