

6.00080.50

PowerMaxx BS Basic

## 10.8 Volt Cordless Drill / Screwdriver PowerMaxx BS Basic



0007900S\_51.EPS

- Light compact drill/screwdriver in extremely short design for versatile use
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Integrated working light to illuminate the work site
- With handy belt hook, can be fixed either on the right or left side without tools
- Practical capacity display for checking the charge status
- Ultra-M technology for highest performance, gentle charging, optimum energy utilisation and long service life.
- 3-year battery pack warranty by means of Ultra-M technology

### Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	10,8 V
Capacity of battery pack	2,0 Ah
Maximum torque, soft	17 Nm
Maximum torque, hard	34 Nm
Adjustable torque	0,5 - 5 Nm
- Drill diameter in	
- Steel	10 mm
- Wood	22 mm
Idle revolutions	0 - 360 / 0 - 1.400 /min
Drill spindle thread	1/2 " - 20 UNF
Chuck adapter	1 - 10 mm
Weight (including battery pack)	0,8 kg

### Scope of delivery

Quick-action Keyless Chuck, Belt hooks, 2 Li-Power rechargeable battery packs (10.8 V/2.0 Ah), Charger LC 40, Plastic Carry Case