

Cordless drill/driver GSR 10,8-2-LI Professional



Cordless drill/driver GSR 10,8-2-LI Professional

The shortest powerful tool
in the 10.8 volt class



Technical data

No-load speed (1st gear /
2nd gear) 0 – 350 / 1.300 rpm

Chuck capacity, min./max. 1 / 10 mm

Battery voltage 10,8 V

Weight incl. battery 0,95 kg

Torque settings 20+1

Drilling diameter

Max. drilling diameter in
wood 19 mm

Max. drilling diameter in
steel 10 mm

Screw diameter

Max. screw diameter 7 mm

Functions

Multiple gears X

Forward/reverse operation X

Electronic X

Auto-Lock X

Softgrip X

Light X

Part number 0 601 868 101

Price 80,00 until 171,00*