

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Squares, Bevels and Gauges
Catalogue number	3533, 3537, 3540, 3541, 3542A, 3543, 3579, 3581 & 3582
Date	04/03/2008

Range Description Squares, bevels and gauges	
Features 3533 • Solid beech handle • Hardened and tempered blue steel blade • 3 rivet attachment for security • Protective brass inside face 3537 • Solid beech handle • Blue spring steel blade • Brass adjustment screw 3540 • Solid Rosewood handle • Hardened and tempered blue steel blade • 3 rivet attachment for security • Protective brass inside face 3541 • Solid Rosewood handle • Blue spring steel blade • Brass lever adjustment screw	 3533  3537  3540  3541

3542

- Solid Beech construction
- Hardened marking pin
- Plastic thumbscrew adjustment



3542

3543

- Solid rosewood construction
- Brass inlays on marking faces for protection
- Screw pin adjustment for accurate and consistent setting of mortice and tenon joints
- Hardened marking pins
- Knurled brass locking screw



3543

3579

- Multi function combination square
- Black metal stock, center and protractor heads
- Stock includes scriber and level
- Protractor clearly defined in black
- Dual metric and Imperial graduations



3579

3581

- Heavy duty stock with brass adjustment screw
- Dual metric and Imperial graduations
- Stock includes level and scriber



3581

3582

- Metal stock with brass adjustment screw
- Dual metric and Imperial graduations
- Stock includes level and scriber



3582

Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
T3533 09	Beech Joiners square 225mm/9"	5013969480900	82055910	3
T3537 09	Beech sliding bevel 225mm/9"	5013969984088	82055910	3
T3540 09	Rosewood Joiners square 225mm/9"	5013969481105	82055910	3
T3540 12	Rosewood Joiners square 300mm/12"	5013969481204	82055910	3
T3541 9	Rosewood sliding bevel 225mm/9"	5013969481402	82055910	4
T3542A	Beech marking gauge 195mm/8"	5013969577204	82055910	3
T3543	Rosewood marking gauge 195mm/8"	5013969481600	82055910	1
T3579	Combination square with protractor and centre	5013969484809	82055910	1
T3581	Heavy duty combination square	5013969485004	82055910	3
T3582	Combination square	5013969485103	82055910	3

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Great Britain

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3533 09	155	18	275	224	Sold loose			
T3537 09	27	37	240	120	Sold loose			
T3540 09	155	18	275	280	Sold loose			
T3540 12	195	18	355	346	Sold loose			
T3541 9	27	22	235	134	Sold loose			
T3542A	77	70	202	124	Sold loose			
T3543	75	55	190	250	Sold loose			
T3579	120	35	305	620	145	36	355	655
T3581	120	18	305	338	145	19	355	372
T3582	120	18	305	270	145	19	355	304

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
T3533 09	205	280	30	760		
T3537 09	160	320	20	376		
T3540 09	205	280	30	910		
T3540 12	220	360	55	1164		
T3541 9	100	300	65	605		
T3542A	117	250	90	500		
T3543	85	225	65	304		
T3579	145	385	37	740		
T3581	160	375	40	1222		
T3582	160	375	40	1010		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3533 09							88	Box
T3537 09					16	Bags		
T3540 09							88	Box
T3540 12							126	Box
T3541 9					4	Bags	65	Box
T3542A							128	Box
T3543					4	Bag	50	Box
T3579	35	Wallet					85	Box
T3581	35	Wallet					106	Box
T3582	35	Wallet					106	Box