



P1 HPDB50M

HPDB50M

MODEL NO:  
P1: M-317/318

HPDB50M	HPDB50M	HPDB50M	HPDB50M
1	1	14	14
26	26	39	39
2	2	15	15
27	27	40	40
3	3	16	16
28	28	41	41
4	4	17	17
29	29	42	42
5	5	18	18
30	30	43	43
8	8	19	19
31	31	44	44
7	7	20	20
32	32	45	45
8	8	21	21
33	33	46	46
9	9	22	22
34	34	47	47
10	10	23	23
35	10	48	23
11	11	24	48
36	11	49	24
12	12	50	24
37	12	50	49
13	13	SHIELD	25
38	13	SHIELD	50
		SHIELD	50
		SHIELD	50

PART	Q' TY	DESCRIPTION
1	2	HPDB50, MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR
2	4	LATCH
3		UL2919, 28AWG, 25 TWISTED PAIRS, ALUM-MYLAR AND COPPER BRAID FOIL SHIELDING, WITH DRAIN WIRE, JACKET BEIGE
4		MOLDED PVC BRIGE
APPROVED		
CHECKED		
DRAWING 劉俊華		
ITEM NO.		SS-101