

DET3TD

Digital Ground Tester



- IP54 rated
- 2 and 3 point testing
- Selectable 25 V or 50 V output
- Complete with lead and stake kit
- Simple one button operation
- Hardwearing carry case
- Delivered with calibration certificate

DESCRIPTION

The new ground testing instrument family from Megger offers a unique solution to your ground rod testing needs. The complete kit of instrument, test leads, stakes, batteries and calibration certificate are delivered in a tough polypropylene carry case - everything you need to start testing in one kit.

The ground tester is rated to IP54 making it truly an outdoor instrument. The ground tester has been designed to be easy to use - a large selector switch makes selection of 2 and 3 pole test easy with gloved hands - and the design makes the fitting of shorting links to perform 2 pole tests a thing of the past. A large, clear, easy to read LCD display and thumb sized test button again makes the instrument particularly suited to the outdoor conditions of ground testing.

In addition to this ease of use, the ground tester also automatically checks the connection and condition of the P and C spike, indicating the status on the display. The instrument also includes a voltmeter to allow you to measure the ground voltage. The ground tester can measure resistance from 0.01 Ω through to 2000 Ω and earth voltages up to 100 V. To allow accurate testing in noisy environments the instrument is capable of rejecting noise of up to 40 V peak to peak.

The Megger digital ground tester is powered by eight AA batteries which are widely available and also give excellent testing time - the status of these batteries is given by a bar graph on the LCD display allowing you to decide when to change the batteries, before they expire.

The Megger ground testers are designed to meet stringent safety standards and are rated CAT IV 100 V.

ELECTRICAL SPECIFICATIONS**Ingress protection:**

IP54

C spike check:

Automatic

P spike check:

Automatic

Noise check:

Automatic

Noise rejection:

40 V pk to pk

2-wire test:

Yes

3-wire test:

Yes

Resistance range:

0.01 to 2000 Ω

Resistance Accuracy:

2% ±3 digits

Earth voltage range:

0 - 100 V a.c.

Earth voltage accuracy:

2% ±2 V

Display

LCD

Battery type:

8 off AA cells

Operating temperature range:

-15 to +55°C

Storage temperature range::

-40 to +70°C

Safety

EN61010-1 CAT IV 100 V

Dimensions:

203 x 148 x 78 mm (8 x 5.7 x 3.2 inches)

Weight:

1 kg

ORDERING INFORMATION

Item (Qty)	Order Code
Digital Tester 2 and 3 terminal	DET3TD
Included Accessories	
Hard carry case	
Stake and wire kit	
Optional Accessories	
Right angled terminal adaptor set	6220-803
2 replacement earth test spikes	6220-804
3 replacement test leads	6220-805

UK

Archcliffe Road, Dover
 CT17 9EN England
 T (0) 1 304 502101
 F (0) 1 304 207342

UNITED STATES

4271 Bronze Way
 Dallas, TX 75237-1019 USA
 T 1 800 723 2861
 T 1 214 333 3201
 F 1 214 331 7399

OTHER TECHNICAL SALES OFFICES

Norristown USA, Toronto CANADA,
 Mumbai INDIA, Trappes FRANCE,
 Sydney AUSTRALIA and the
 Kingdom of BAHRAIN.

ISO STATEMENT

Registered to ISO 9001:2000 Cert. no. Q 09250
 Registered to ISO 14001-1996 Cert. no. EMS 61597

DET3TD_DS_en_V01

www.megger.com

Megger is a registered trademark