



RevNo	Revision note	Date	Signature	Checked
-------	---------------	------	-----------	---------



NOTES:

- 1:100% short,open and miss wire test.
- 2:Insulation resistance:DC200V 10MΩ(Min)  
Conduction resistance 5Ω(Max)
- 3:Screws need to install in the P1 side.



⑦	SCREW	THUMB SCREW #4-40*15	2	PCS
⑥	NUT	NUT-NICKEL PLATED #4-40	2	PCS
⑤	OUTER MOLDED	BLACK 45P PVC	0.024	KG
④	INNER MOLDED	LDPE	0.024	KG
③	CONNECTOR	USB A/FEMALE,GOLD PLATED PIN,NICKEL PLATED SHELL,WHITE INSULATION	1	PCS
②	CONNECTOR	USB B/FEMALE,GOLD PLATED PIN,NICKEL PLATED SHELL,WHITE INSULATION	1	PCS
①	CABLE	UL2725 28AWG*1P+24AWG*2C+AL-FOIL+D(7/0.12BC)+BRAID(64/0.1CCS) BLACK PVC JACKET,OD;∅4.8±0.2MM	220	MM
NO.	MATERIAL	DESCRIPTIONG	QTY.	UNIT

Ltemref	Quantity	Title/Name,designation,material,dimension etc		Article No./Reference	
Designed by ACHY	Checked by HELEN	Approved by - date OCT 31.2013	File name USB AF/BF 0.135M	Date OCT 31.2013	Scale FREE
ANGLE:				ADAPTOR LEAD, USB B TO A, SOCKETS, 135MM	
UNIT:MM				AV23286(PSG03801)	Edition 1 Sheet 1/1