


NOTES:
 1:100% short,open and miss wire test.
 2:Insulation resistance:DC200V 10MΩ(Min)
 Conduction resistance 5Ω(Max)
 3:Screws need to install in the P1 side.



⑥	SCREW	THUMB SCREW #4-40*14	2	PCS
⑤	NUT	NUT-NICKEL PLATED #4-40	2	PCS
④	OUTER MOLDED	BLACK 45P PVC	0.024	KG
③	INNER MOLDED	LDPE	0.024	KG
②	CONNECTOR	HDMI A TYPE FEMALE,THE PIN GOLD PLATED,THE SHELL FOR NICKEL PLATING	2	PCS
①	CABLE	28AWG*1P+D+FAM)*5+28AWG*4C+ADB(80/0.12AL-MG),JACKET:BLACK PVC, OD:3.2*14.5±0.2mm	240	MM
NO.	MATERIAL	DESCRIPTIONG	QTY.	UNIT

Ltemref	Quantity	Title/Name,designation,material,dimension etc	Article No./Reference		
Designed by ACHY	Checked by HELEN	Approved by - date OCT 31.2013	File name HDMI 1.4 AF/AF 0.165M	Date OCT 31.2013	Scale FREE
ANGLE:	ADAPTOR LEAD, HDMI, SOCKETS, 165MM				
UNIT:MM	AV23289(PSG03804)		Edition 1	Sheet 1/1	