


SPECIFICATIONS				
CONTACT CARRIER MATERIAL/COLOR	NYLON or PBT/GRAY			
MOLDED HEAD MATERIAL/COLOR	TPU/BLACK			
CONTACT MATERIAL/PLATING	BRASS/GOLD			
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL			
RATED CURRENT [A]	9.0 A (18 AWG), 2.0 A (22 AWG)			
RATED VOLTAGE [V]	150 V			
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW			
CONDUCTOR INSULATION MATERIAL	PVC			
NUMBER OF CONDUCTORS [AWG]	3x18 AWG, 8x22 AWG			
DRAIN/SHIELD	22 AWG DRAIN/POLYESTER FOIL SHIELD			
TEMPERATURE RANGE	-40° C to $+105^{\circ}$ C (-40° F to $+221^{\circ}$ F)			
PROTECTION CLASS	IEC IP67			



2.

3.

FINISH

SEE SPECIFICATIONS

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

30-49mm

50-69mm

70-100mm

OVER 100mm

2. STRIP AND TIN LENGTHS ARE FOR REFERENCE ONLY: SOME LENGTHS MAY NOT BE STRIPPED AND TINNED.

F	DRAWING PROCESSED AS PART OF ECO 33971	СВМ	04/06/11	33971
REV	DESCRIPTION	BY	DATE	ECO NO.

±2.0mm

±3.0mm

±4.0mm

RELATED DOCUMENTS 3RD ANGLE PROJECTION THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT turck inc WITHOUT WRITTEN PERMISSION IS High Technology Sensors and Automation Controls PROHIBITED. MATERIAL DATE 09/26/00 DESCRIPTION JBJ ALL DIMENSIONS SEE SPECIFICATIONS DISPLAYED ON THIS DRAWING ARE FOR

REFERENCE ONLY

CONTACT TURCK FOR MORE

INFORMATION

UNIT OF MEASUREMENT

SCALE 1=1.3 MILLIMETER [INCH]

3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com

CKM 19-11-*

IDENTIFICATION NO. REV

DO NOT SCALE THIS DRAWING

FILE: 777000016 SHEET 1 OF 1

SOURCE DRAWING - FOR REFERENCE ONLY