

## 5 Pieces 4 In.6 TPI Speed for Wood T-Shank Jig Saw Blades T244D

- Designed for curved and fast cuts in hard and soft wood, OSB, plywood 1/4 In. to 2-3/8 In. thick
- 6 TPI tooth profile and high carbon steel blade body for exceptionally fast cutting and long life in wood
- 4 In. overall length, 3 In. usable length
- 5 piece pack



### Specifications: T244D 5 Pieces 4 In.6 TPI Speed for Wood T-Shank Jig Saw Blades

Type	Speed for Wood
Teeth Per Inch	5-6
Overall Length	4"
Application	Hard/soft woods, OSB, plywood 1/4"- 2-3/8"
Type of Cut	Scroll blade for curved and fast cuts
Quantity	5
Tooth Design	Side set and ground
Material	High Carbon Steel
Working Length	3"
Blade Thickness	0.05"
Blade Height	0.24"