

Adjustable Spanners



Description:

Made of Chrome Vanadium Steel, Chrome Plated for heavy duty. ANSI Standard.

Part Number Table

Description	Item - Size	Max. Capacity (mm)	Box/Ctn	Part Number
Spanner, Adjustable, Chrome Plated, 4"	AW100 - 4"	13	6/120	005-005-04
Spanner, Adjustable, Chrome Plated, 6"	AW150 - 6"	21	6/120	005-005-06
Spanner, Adjustable, Chrome Plated, 8"	AW200 - 8"	29	6/60	005-005-08
Spanner, Adjustable, Chrome Plated, 10"	AW250 - 10"	31	6/48	005-005-10
Spanner, Adjustable, Chrome Plated, 12"	AW300 - 12"	36	6/24	005-005-12
Spanner, Adjustable, Chrome Plated, 15"	AW375 - 15"	45	4/24	005-005-15
Spanner, Adjustable, Chrome Plated, 18"	AW450 - 18"	55	2/12	005-005-18
Spanner, Adjustable, Chrome Plated, 24"	AW600 - 24"	62	1/6	005-005-24