



TongFang Global Limited

Model Number : LE-39GCL-P	39 inch DLED HDTV
UPC Code	
Display Features	
Diagonal Panel Size	38.5 inch
Active Area	853.41 (H) x 479.81mm (V)
Aspect Ratio	16:9
Panel Resolution	1366 x 768
Panel Refresh Rate	60Hz
Brightness	200 ~ 250 cd/m2
Dynamic Contrast ratio	2400~3000:1
Viewing Angle	178°(H) x 178°(V)
Dot Pitch	0.62475mm (H) x 0.62475mm (V)
Maximum Color	16.7 M
Response time Gray-Gray	6.5ms
Electronics	
Scaler Solution	SIS231
DNR	3D
Digital Comb Filter / Type	3D
TV System & Video Standards Supported	
TV System	PAL/SECAM(B/G,D/K,I,L/L') /DVB-T
Max Storage Channels	100(ATV) / ≥1200(Dynamic)(DTV)
Composite / S-Video input	PAL/NTSC/SECAM
Video Connections	
Analog&Digital TV Tuner	x1
Composite Video Input	x1
S-Video Input (4pin DIN)	NO
Mini Component Input (Y,Cb,Cr/Y,Pb,Pr)	x1

VGA Input (15 pin D-Sub)	x1
DVI-D / DVI-I Input	NO
HDMI Input	x3
SCART Input	1
CI Slot In	1
USB	x1
Audio	
Maximum Audio Output	2x6W
Number of speakers	x2
Audio Surround	Yes
Audio Connections	
Stereo Mini Phono Jack Input (3.5mm)	x1(VGA Audio)
RCA Input	x1(R/L)
Headphone: Stereo Mini (3.5mm)	x1
RCA Output	NO
Coax Digital Output	x1
VGA Resolutions Supported	
640x480	
800x600	
1024x768	
1360x768	
This spec may change from time to time,we are not liable for any	

Update Date:

16-Nov-13

Version: 1

Features	
Built in 3D PAL/NTSC Comb Filter	
Built in 3D Video Noise Reduction	
Built in NICAM/A2	
Support 1000pages Teletext	
Support PVR/Playback	
Digital/Analog Channel auto tuning	
MHEG-5(UK)/Favorite Channel Edition/Subtitle/Audio Language	
Component &HDMI support :480I,576I,480P,576P,720P,1080I ,1080P	
USB Support File Format : MPEG-1/-2,MP3,JPEG	
OSD Language : English/French/Spanish/German/Italian/Portuguese	
Accessories Included	
Remote Control / Battery Included / Mini Component Cable	
User Manual / Quick Start Guide	
Power Requirements	
Power Source	AC100-240V 50/60Hz
Power ON consumption	< 70W
Standby consumption	< 0.5W
Operating Temperature	5 -35
Operating Humidity	20%-80%
Dimension (WxHxD) cm	
VESA Dimension (WxH)	20.0x20.0
Unit w/ Stand	89.10x57.30x21.20
Unit w/o Stand	89.10x53.00x8.70
Carton	97.10x62.50x17.50
Weight (kg)	
Net Weight w/Stand	7.6 kg

Net Weight w/o Stand	7.2 kg
Gross Weight	10.kg

Warranty & Support

One Year Manufacture Warranty
Toll Free Customer Support
On-Line Manual / Firmware Access

Logistic

Standard Pallet Unit Load	
20' GP Container Unit Load w/o Pallet	234
40' GP Container Unit Load w/o Pallet	468
40' HQ Container Unit Load w/o Pallet	624



misrepresentation if we post the wrong specs on the sheet