

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BE-2R

BE-2R

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-2584

M

DRAWING NUMBER

26

X 3


ISSUE

3

CHECK

REVISIONS

A	CO	32144	GLH	26 JUL 73
B	CO	3036627	C J H	8 APR 76
C	CO	58782	W J M	24 JAN 86
D	CO	77590	S A D	10 JUN 94
E	CO	94212-C	D L T	20 SEP 99



NOTE
 ▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — 14 — 22 OZ
 RELEASE FORCE — — — — 10 OZ MIN
 DIFFERENTIAL TRAVEL — — .0020 — .0075
 OVERTRAVEL — — — — .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 S P D T
 25-A-125, 250, 480 VAC 1 HP-125 VAC;
 2 HP-250 OR 480 VAC; PILOT DUTY
 750 VA-480 VAC, MAX; 60/75°C (Cu)



SCALE FULL

DO NOT SCALE PRINT
 UNLESS OTHERWISE NOTED
 DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
 ONE PLACE (.0) ± .030
 TWO PLACE (.00) ± .015
 THREE PLACE (.000) ± .005
 ANGLES ±

WEIGHT .063 LB

FORMTEK

FO-50378-1A

DRAWN

CHECK

D B W 20 APR 72

SD

SD

SD