



• PowerCore™ • Surge Protection • Networking • Mobility • USB • FireWire™ • Computer Cables

## CAT 5E RJ45 Ethernet Patch Cable 24-Karat Quality CAT5E Patch Cable for Connecting Your Ethernet Peripherals to your Network GPNC-5CC-XX\*

Without a way to connect computers to one another you cannot have a network. As a result your network is only as good as your infrastructure. Improve your network's connectivity with Cat5E patch cables from GoldX® products. Gold on the connectors ensures the best level of conductivity between the cable and your network peripherals. Designed according to the TIA/EIA 568 B-2 specification.



### Featured Product Benefits

- Premium Quality
- Gold Plating on connectors
- Supports 10 Mbps, 100 Mbps & Gigabit Ethernet

\*CC = Color

\*XX = Length

*CAT 5e*



† Key for Colors

BK=Black, BL=Blue, GR=Green, GY=Gray, OR=Orange, PK=Pink, PU=Purple, RE=Red, WH=White, YL=Yellow

Item Number		Length
GPNC-5_-01	_= GY †	1 Feet
GPNC-5_-02	_= BK, BL, GY †	2 Feet
GPNC-5_-03	_= BK, BL, GR, GY, OR, PU, RE, WH, YL †	3 Feet
GPNC-5_-04	_= GY †	4 Feet
GPNC-5_-05	_= BK, BL, GY, OR, RE, YL †	5 Feet
GPNC-5_-07	_= BK, BL, GY, OR, PK, PU, RE, YL †	7 Feet
GPNC-5_-10	_= BK, BL, GR, GY, PK, PU, RE, YL †	10 Feet
GPNC-5_-14	_= BK, BL, GR, GY, OR, PK, PU, RE, YL †	14 Feet
GPNC-5_-15	_= BK, GY †	15 Feet
GPNC-5_-25	_= BK, BL, GR, GY, PK, RE, YL †	25 Feet
	GPNC-5_-40	40 Feet
GPNC-5_-50	_= BK, BL, GR, GY, OR, PU, RE, YL †	50 Feet
GPNC-5_-75	_= BL, GR, GY, OR, RE, WH †	75 Feet
GPNC-5_-100	_= BL, WH, YL †	100 Feet

© Copyright 2007 Jo-Dan International, Inc. all rights reserved. Plus Series®, PowerCore®, QuickConnect®, Share Plus®, and GoldX® Products are registered trademarks of Jo-Dan International, Inc. All other trademarks and registered trademarks are the property of their respective owners. Designed in USA. Made in China. One or more of the following patents may apply: D494,935, D494,934, D494,932, D493,453, 6,755,676, D490,702, 6,736,658, 6,726,509, 6,716,047, D485,752, D484,044, D481,629, D481,628, 6,607,408, D478,001, D478,000, D468,635, 6,479,607, D465,223,6,454,584, D462,612, D452,427, D452,426, D451,888, D451,480, D450,303, D448,736, D444,772, D443,862, D443,593, D442,919, D442,566, D442,555, 5,788,521, 5,658,158, 5,334,033, 5,292,257. D503,882; 6,843,684; 6,854,989; 6,872,086; D506,386; 6,905,374; D509,797; 6,991,483; D513,976; 7,004,787; 7,028,114; D519,925; D522,507; 7,258,572. Other patents pending.

(866) 24-GOLDX

[www.goldxproducts.com](http://www.goldxproducts.com)