

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

34062-0007

Status:

Active

Overview:

MX150™ Sealed Connector System

Description:

MX150™ Cable Sealed Female Connector, Single Row, 2 Circuits, Polarization C, with Connector Position Assurance, Black



Documents:

3D Model

Drawing (PDF)

Application Specification AS-34062-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	34062
Application	Power
Comments	with Connector Position Assurance (CPA)
MolexKits	Yes
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX150™ Sealed Connector System
Product Name	MX150™
UPC	756054705025
Physical	
Circuits (maximum)	2
Circuits Detail	2
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.520/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C
Electrical	
Current - Maximum per Contact	15A

Material Info

Reference - Drawing Numbers

Application Specification

Sales Drawing

AS-34062-000

SD-34062-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

34062Series

Mates With

Direct Connect only

Use With

34083 Tin (Sn) Cable Seal Female Terminal, 34081 Gold (Au) Cable Seal Female Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION