

Compact 1-stage filter for 3-phase systems with neutral conductor



Description

- Quick-connect terminals 6.3 x 0.8 for three phases, neutral conductor and ground
- High symmetrical and asymmetrical attenuation
- In the frequency range from 10kHz up to 300MHz

Standards

- IEC 60939
- UL 1283

Approvals

- VDE Certificate Number: 40004673

Applications

- Especially designed for industrial applications such as: Frequency Converters, Stepper Motor Drives, UPS-Systems, Inverters
- Suitable for use in equipment according to IEC/UL 60950

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)


Technical Data

Rated Current	3 - 20 A @ Ta 40 °C
Rated voltage	250/440 VAC, 50/60 Hz
Approval for	3 - 20 A / 250/440 VAC; 50 Hz
Overload Current	1.5 x Ir
Leakage Current	industrial < 3 mA (440 V / 50 Hz)
Dielectric Strength	250/440 VAC: 2.25 kVDC between L-L 1.7 kVDC between L-N 3 kVDC between L-PE 2.7 kVDC between N-PE Test voltage (2 sec)
Number of Filter Stages	1-stage
Weight	0.2 - 0.35 kg
Material: Housing	Metal
Sealing Compound	UL 94V-0

Mounting	Screw-on mounting on chassis, from top
Terminal	Quick connect terminals 6.3 x 0.8 mm
Operating Temperature [°C]	-25 °C to 100 °C
Climatic Category	25/100/21 acc. to IEC 60068-1
Degree of Protection	IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
MTBF	> 200'000h acc. to MIL-HB-217 F


Dimension

Case 47



- 1) Line
2) Load

Diagrams






Attenuation Loss

--- differential mode ____ common mode

Standard version
3A (FMW-65-0001)



6A (FMW-65-0002)

10A (FMW-65-0003)



Industrial version
10A (FMW-65-0004)

20A (FMW-65-0005)



All Variants

Rated Current [A]	Rated Voltage [VAC]	Leakage Current [mA]	L [mH]	Cx [μF]	Cy [nF]	Weight [kg]	Housing	Order Number
3	250/440	0.5	1	0.1	4.7	0.2 kg	47	FMW-65-0001
6	250/440	0.5	0.5	0.1	4.7	0.2 kg	47	FMW-65-0002
10	250/440	0.5	0.4	0.1	4.7	0.23 kg	47	FMW-65-0003
10	250/440	3	0.4	0.1	22	0.35 kg	47	FMW-65-0004
20	250/440	3	0.15	0.1	22	0.25 kg	47	FMW-65-0005

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 10 Pcs