



US-101

USB 1 Port RS232 1MBaud

Description

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"

Features

Product

- 1 x RS232
- USB 2.0
- 128 Byte TX and 256 Byte RX FIFOs
- Up to 921,600 Baud
- DB9 Connector 9 Pin Male
- Includes 0.25mm USB Extender cable
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software

US-101:

1MBaud

USB 1 Port RS232

- Lifetime Support
- Lifetime Warranty (registration required)

USB to Serial adapter providing one RS232 serial port. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 256 byte receive FIFOS, coupled with 1Mbit line drivers deliver uncompromising performance on your laptop/PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8 with additional drivers for both Mac OS X and Linux.

USB to serial is the quick low cost way to connect your computer to a serial comms enabled device. Boost software gives industry leading functionality and compatibility.

These products do away with traditional issues with USB technology so you can buy with confidence!

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 8 32 bit 64 bit Editions
- Windows 7 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows XP 32 bit 64 bit editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.

13

ORDER
Description
USB 1 Port RS232 1MBaudCode
US-101Image: Comparison of the compar

+44(0) 151 220 2500 sales@brainboxes.com www.brainboxes.com

US-101 - USB 1 Port RS232 1MBaud

US-101: Full Specification

Port	Ports	1 x RS232
Pin 1 DCD RS232 Pinout (9 Pin Male)	Connector	DB9 Connector - 9 Pin Male
Pin 2 RXD Pin 3 TXD Pin 4 DTR Pin 5 GND	FIFO Size	256 Rx FIFO + 128 Tx FIFO
	Operating Distance	EIA - RS232 Standard
Pin 6 DSR Pin 7 RTS Pin 8 CTS Pin 6 Pin 9	Cable	USB extender cable 0.25 metre 1ft
Pin 8 CTS Pin 6 Pin 9 Pin 9 RI RI		
Port Settings	Baud Rate	921,600
921,600 > > > > > baud	Data Bits	7 or 8
	Parity	Odd, Even, None, Mark or Space
	Stop Bits	1 or 2
	Flow Control	
	Tx/Rx Modes	Point to Point
Interface	OS Compatibility	Microsoft Windows 8 32 bit 64 bit Editions
		Microsoft Windows 7 32 bit 64 bit Editions
		Windows Server 2008 32 bit 64 bit Editions
		Windows Vista 32 bit 64 bit Editions
		Mac OS X
	BUS	USB 2.0
Approvals	Other Approvals	AEO C-TPAT C-Tick
Vindows-7		Microsoft Certified Gold Partner WEEE
		RoHS METL UL
	Microsoft Approvals	Windows 7 32 bit 64 bit Editions
		Windows Vista 32 bit 64 bit editions
		Windows XP 32 bit 64 bit editions
General	PCB Layers	4
la Blannath	Power Consumption	40mA @ 5V
Microsoft Gold Partner	Product Weight	0.023 kg
N136	Product Size	89l x 35w x 20h mm
Box Content	Packaging	Cable, Installation CD (inc manual, Microsoft signed drivers & Utili- ties)
	Device	USB 1 Port RS232 1MBaud USB extender cable 0.25 metre 1ft
Product Support	Warranty	Lifetime (online registration required)
	Support	Lifetime Web, Email & Phone Support from fully qualified, friendly staff who work in and alomgside our Product Develop- ment Team
Additional	OEM Option	Available for bulk buy OEM
	Made In	Manufacturerd in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"
	Customisable	Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More info: sales@brainboxes.com

+44(0) 151 220 2500 sales@brainboxes.com www.brainboxes.com