



Product information



WXD 2

Code No.: T0053426699

Power unit

Soldering and desoldering station, 2 channels 200 W (255 W)

Technical Data

| | This station is ESD safe. |
|-------------------------------|--|
| Dimensions L x W x H: | 170 x 151 x 130 mm (6,69 x 5,94 x 5,12 inch) |
| Weight: | approx. 3,8 kg |
| Channels: | 2 |
| Power supply: | 230 V, 50 Hz |
| Power consumption: | 200 W (255 W) |
| Protection class: | I |
| Fuse: | T2A |
| Temperature accuracy: | ± 9°C (± 17°F) |
| Temperature stability: | ± 2°C (± 4°F) |
| Pump (periodic duty 30/30 s): | Max. pressure 0,7 bar |
| Air consumption: | 35 1/min |
| Display | |
| Dimensions touch panel: | 74 x 38 mm |





| Resolution: | 255 x 127 (128) dots |
|--------------------------|--|
| Display backlighting: | 4 LEDs |
| Equipotentional bonding: | The 3,5 mm switch offers four different options: a) Hard grounded without plug (original delivery) b) Equipotential bonding: with plug, compensation line on center contact c) Potential free: with plug |
| | d) Soft grounded: with plug and soldered resistor grounded via selected resistor |
| USB interface: | USB interface in front of firmware updates, parameterization and monitoring USB interface supports all standard USBflash drive types |