



RoHS compliant

3	15	Signal contact	P0 / Brass	AuroPur / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	green
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	

Measurement without tolerance occ. to ISO 2768-m NAME / DATE Markus Jobst 07-07-2010 CHECKED bigli.rnber 08-07-2010		SCALE 2:1	TITLE D-Sub Mixed-Layout Connector
DRAWN CHECKED	ORIGINAL DIN A3 DRAWING AS A FILE <b>FST group</b> fctgroup.com		
REV. 1	DATE	CH.-NO.	DWG.NO. FM17W2PA-K120 REPLACEMENT FOR:
1			REV. 1 PAGES 1

ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE REPRODUCED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.