


3	15	Signal contact	SO / Brass	AuroPur / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	green
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	
TITLE				
Measurement without tolerance acc. to ISO 2768-m SCALE 2:1				
NAME / DATE Markku Jobst 07.07.2010				
DRAWN				
CHECKED				
Digitrinder 08.07.2010				
 fctgroup.com				
ORIGINAL: DIN A3-DRAWING AS A FILE				
REV.	1	DATE	CH-NO.	DWG. NO.
				FM17W2SA-K121
REPLACEMENT FOR:				PAGES 1

D-Sub Mixed-Layout Connector

REV. 1

PAGES 1

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE REPRODUCED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.