CMS 450.V2 DOTTY

- Facility of use
- 5 Differents functioning modes
- Best quality/price ratio for performance without equal
- Compacts & ergonomic
- 10 programmes available
- Compatible for automatic dispensing on 3 axis CNC machine (Technodrill)

Dispenser unit for dosing of glues, solder pastes as well as low viscosity products.
The dispenser DOTTY CMS 450.V2 can work autonomous or in combination with a pick & place unit.

The DOTTY dispenser can work under many different ways :

- **Manual**: pushing on the pedal, the product deposit will be done when the control is done. Getting of the pedal will stop the deposit

- **Semi-automatic**: pushing on the pedal, a x quantity of deposit is done once. You need to push again on the pedal to start a new deposit.

- **Automatic** : remaining on the pedal, a x quantity deposit is done every x repetitions until the pedal is getting of.

- **Learning** : This programm automatically defines deposit and repetition times according to work to do. You just need to make 10 manual deposits depending on the requested rate and the unit will analyse, making an average of appropriate times. Once learning mode is finished, the unit will get back to automatic mode.

The dispensers are delivered complete wit a set of needles, a set of suction cups, a 10cc syringe, a foot pedal control.
To be connected to a compressed air network or on a compressor.

TECHNICAL CHARACTERISTICS

Available use modes : **5**
Manual : **Yes**
Semi-automatic : **Yes**
Automatic : **Yes**
Learning : **Yes**
Max. pressure : **7 bars max.**
Power : **14 W**
Sound level : **<40 dB (A)**
Using pressure : **0,1 to 7 bars**
External dim. L x l x H (mm) : **260 x 140 x 140 mm**
Net weight : **2.0 Kg**
Power supply : **230 V - 50 Hz**

Reference : **F41020.1**