

MS216B

Pos-E-Kon™

Male screw terminal insert



General

Type:	16 A 600 VAC
T&B UPC:	78621011846
T&B Status:	M
Series:	B series
Flammability:	UL94 V-0
Approvals:	MEIE, EZU, SEV
Housing Temperature Range:	-40°C/-40°F to +125°C /+257°F
Insert Material:	Glass-filled thermoplastic
Insert Temperature Range:	-40°C/-40°F to +125°C /+257°F
Rated Voltage:	600 VAC
Screw Terminal:	20–14 AWG
Test Voltage:	3 kV eff.
Working Current:	16 A max.
Special Features:	IP65 locked positions per DIN VDE 0470, IEC 529
Material:	Die-cast aluminum alloy

Dimension Information

AWG:	20–14 AWG (0.5–2.5 mm ²)
Contact Material:	Solid drilled copper alloy
Contact Resistance:	# 1milliohm
Contact Surface:	Hard silver plated, Hard gold plated
Contact Type:	16 contacts with ground connection
Crimp Terminal:	20–12 AWG
EPDM Seal Gaskets:	Epoxy powder-coat finish